



KN04P

Phase terminal,gamma,4x2,5-16mm²,90A

Technical properties

Architecture

Number of poles	1 P
Fixing mode	Clipped

Functions

Suitable for fine strand conductors	Yes
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	Yes
Suitable for extra fine-strand conductors without cable end sleeve	No

Electric current

Rated current	63 A
---------------	------

Connection

Conductor cross section, input AWG	2.5 / 16
Conductor cross section, output AWG	2.5 / 16

Settings

terminal type	Phase terminal
---------------	----------------

Equipment

Number of outputs	3
Number of inputs	1

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes