



KN14N

**Terminal, QuickConnect, neutral, 14 connections**

**Technical properties**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole    | 1 P |

**Functions**

|                            |     |
|----------------------------|-----|
| Suitable for flexible core | Yes |
|----------------------------|-----|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Dimensions**

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 34 mm |
| Height of installed product | 33 mm |
| Width of installed product  | 60 mm |

**Materials**

|                              |          |
|------------------------------|----------|
| Copper weight of the product | 0.015 kg |
|------------------------------|----------|

**Connection**

|  |                          |
|--|--------------------------|
| Conductor cross-section (flexible), with wire end sleeve | 1.5...25 mm <sup>2</sup> |
| Conductor cross-section (rigid)                          | 1.5...25 mm <sup>2</sup> |

**Settings**

|               |            |
|---------------|------------|
| terminal type | N terminal |
|---------------|------------|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|