



KR95P

**DIN rail terminal 95-240mm<sup>2</sup>, gray**

**Technical properties**

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 232 A |
|---------------|-------|

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 82.8 mm |
| Height of installed product | 97.6 mm |
| Width of installed product  | 25 mm   |

**Connection**

|   |                         |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 25 / 95mm <sup>2</sup>  |
| Connection cross-sect. rigid cable        | 2,5 / 95mm <sup>2</sup> |
| Type of connection                        | with screw              |

**Settings**

|               |                  |
|---------------|------------------|
| terminal type | In-line terminal |
|---------------|------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |