



KXA02LH

Feed-through terminal -phase , 2,5mm², 800V-24A, screw connection

Technical properties

Electric current

Rated current	24 A
---------------	------

Dimensions

Depth of installed product	5 mm
Height of installed product	48.5 mm
Width of installed product	44.5 mm

Connection

Connection cross-sect. flexible conductor	0,5 / 2,5mm ²
Connection cross-sect. rigid cable	0,5 / 4mm ²
Terminal cross-section	4 mm ²
Type of connection	with screw

Settings

terminal type	Feed-through terminal
---------------	-----------------------

Safety

REACH conform	Yes
RoHS conform	Yes