



KXA04LH

**Feed-through terminal-phase , 4mm<sup>2</sup> , 800V/32A, screw connection**

**Technical properties**

**Main electrical features**

Rated operational voltage Ue	800 V
------------------------------	-------

**Electric current**

Rated current	32 A
---------------	------

**Dimensions**

Depth of installed product	6 mm
----------------------------	------

Height of installed product	48.5 mm
-----------------------------	---------

Width of installed product	44.5 mm
----------------------------	---------

**Connection**

Connection cross section (solid-core)	0.5 ; 6 mm <sup>2</sup>
---------------------------------------	-------------------------

Connection cross section (fine-strand)	0.5 ; 4 mm <sup>2</sup>
--	-------------------------

Connection cross-sect. flexible conductor	0,5 / 4mm <sup>2</sup>
---	------------------------

Connection cross-sect. rigid cable	0,5 / 6mm <sup>2</sup>
------------------------------------	------------------------

Terminal cross-section	6 mm <sup>2</sup>
------------------------	-------------------

Type of connection	with screw
--------------------	------------

**Settings**

terminal type	Feed-through terminal
---------------	-----------------------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----