



KXA04LH

Feed-through terminal-phase , 4mm² , 800V/32A, screw connection

Technical properties

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 800 V |
|------------------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Dimensions

| | |
|----------------------------|------|
| Depth of installed product | 6 mm |
|----------------------------|------|

| | |
|-----------------------------|---------|
| Height of installed product | 48.5 mm |
|-----------------------------|---------|

| | |
|----------------------------|---------|
| Width of installed product | 44.5 mm |
|----------------------------|---------|

Connection

| | |
|---------------------------------------|-------------------------|
| Connection cross section (solid-core) | 0.5 ; 6 mm ² |
|---------------------------------------|-------------------------|

| | |
|--|-------------------------|
| Connection cross section (fine-strand) | 0.5 ; 4 mm ² |
|--|-------------------------|

| | |
|---|------------------------|
| Connection cross-sect. flexible conductor | 0,5 / 4mm ² |
|---|------------------------|

| | |
|------------------------------------|------------------------|
| Connection cross-sect. rigid cable | 0,5 / 6mm ² |
|------------------------------------|------------------------|

| | |
|------------------------|-------------------|
| Terminal cross-section | 6 mm ² |
|------------------------|-------------------|

| | |
|--------------------|------------|
| Type of connection | with screw |
|--------------------|------------|

Settings

| | |
|---------------|-----------------------|
| terminal type | Feed-through terminal |
|---------------|-----------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|