



L2222



**Flexible slotted panel trunking halogenfree 20mm Länge = 500mm light grey**

**Technical properties**

**Architecture**

Flexible Yes

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Length 500 mm

Slot width 8 mm

Tongue width 4.5 mm

**Cover, door**

Lid shape none

**Materials**

Colour light grey

Material Polyamid (PA)

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Fixing type selfadhesive and bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 18

Internal/useful cross section 154 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 13

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 20

**Standards**

European directive RoHs voluntary compliance

UL 94 classification V0

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free

Yes

**temperatur**

---

Ambient temperature

-25...90 °C