



L2232



Flexible slotted panel trunking halogenfree 30mm Länge = 500mm light grey

Technical properties

Architecture

Flexible Yes

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Length 500 mm

Slot width 8 mm

Tongue width 4.5 mm

Cover, door

Lid shape none

Materials

Colour light grey

Material Polyamid (PA)

Material group plastic

Type of surface treatment untreated

Installation, mounting

Fixing type selfadhesive and bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 46

Internal/useful cross section 379 mm²

Number of wires 2,5 mm² - 40% filling degree 30

Number of wires 1,0 mm² - 40% filling degree 57

Standards

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

REACH conform Yes

RoHS conform Yes

Halogen free

Yes

temperatur

Ambient temperature

-25...90 °C