



L2733UNLA



L 2733 Untreated End cap

Technical properties

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Compatibility

| | |
|-----------------------|----|
| Product compatibility | LF |
|-----------------------|----|

Connectivity

| | |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

Dimensions

| | |
|-----------------|-------|
| Trunking height | 18 mm |
|-----------------|-------|

| | |
|----------------|-------|
| Trunking width | 19 mm |
|----------------|-------|

Materials

| | |
|----------------|-------|
| Material group | metal |
|----------------|-------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP30 |
|---------------------|------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|