




L2752VERZ



L 2752 galv External corner

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 30 mm

Trunking width 45 mm

Measure a 150 mm

Measure b 200 mm

Cover, door

Lid with softlip -

Materials

Material Steel

Material group steel

Type of surface treatment Galvanised

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP30

Use conditions

Operating temperature -5...60 °C