



L2753UNLA



L 2753 galv End cap

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	30 mm
-----------------	-------

Trunking width	45 mm
----------------	-------

Materials

Material group	metal
----------------	-------

Type of surface treatment	untreated
---------------------------	-----------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------