



L2755VERZ



L 2755 galv Flat corner

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	30 mm
Trunking width	45 mm
Measure a	170 mm
Measure b	100 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	zinc coated
Material	Steel
Type of surface treatment	Galvanised

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------