



L27569010



L 2756 White 9010 T piece LFS 30045

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	30 mm
Trunking width	45 mm
Measure a	340 mm
Measure b	302 mm
Measure c	150 mm
Measure d	170 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Material group	steel
Type of surface treatment	Painted

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------