




L2756VERZ



**L 2756 galv T piece**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Configuration**

Antibacterial treatment No

**Dimensions**

Trunking height 30 mm

Trunking width 45 mm

Measure a 340 mm

Measure b 302 mm

Measure c 150 mm

Measure d 170 mm

**Cover, door**

Lid with softlip -

**Materials**

Material Steel

Material group steel

Type of surface treatment Galvanised

**Installation, mounting**

Base punching Without base punching

**Accessories included**

Accessory configuration Base and lid

**Standards**

European directive RoHS voluntary compliance

**Safety**

Protection index IP IP30

**Use conditions**

Operating temperature -5...60 °C