



L27719010



Internal corner for trunking tehalit.EK 40x40mm pure white

Technical properties

Architecture

Fixing mode Hold in position thanks to lid

Dimensions

Trunking height 40 mm

Trunking width 40 mm

Cover, door

Lid with softlip -

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PVC

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Protection index IP IP40

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK07

temperatur

Ambient temperature -5...65 °C