



L27809010

Junction piece for trunking EK and ATA 12x20, 6/12x30mm pure white

Technical properties

Dimensions

Trunking height	40 mm
Trunking width	40 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Material	PVC
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

temperatur

Ambient temperature	-5...65 °C
---------------------	------------