



L43519010

**T-piece for GBD 50x100mm of ABS in pure white**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

Product compatibility	GBD
-----------------------	-----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	50 mm
Length	110 mm
Trunking width	100 mm

**Cover, door**

Lid with softlip	No
Cover attachment clamping	No
Cover width 1	0 mm
Cover width 2	0 mm
Cover width 3	0 mm
Number of lids mountable	0

**Materials**

RAL colour	RAL 9010 - Pure white
Material	ABS
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-30...90 °C
<b>temperatur</b>	
Ambient temperature	-5...65 °C