



L43559010

T-piece for GBD 50x160mm of ABS in pure white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	GBD
-----------------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	50 mm
Length	180 mm
Trunking width	160 mm

Cover, door

Lid with softlip	No
Cover attachment clamping	No
Cover width 1	0 mm
Cover width 2	0 mm
Cover width 3	0 mm
Number of lids mountable	0

Materials

RAL colour	RAL 9010 - Pure white
Material	ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-30...90 °C
temperatur	
Ambient temperature	-5...65 °C