



L43619010

Internal corner for GBD 56x105mm of PVC in pure white

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Compatibility

Product compatibility GBD

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 56 mm

Length 110 mm

Trunking width 105 mm

Cover, door

Lid with softlip No

Number of lids mountable 0

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 97 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Use conditions

Operating temperature -5...60 °C