



L43819010

**Internal corner for GBD 56x163mm of PVC in pure white**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Compatibility**

Product compatibility	GBD
-----------------------	-----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	56 mm
Length	110 mm
Trunking width	163 mm

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	83 / 97 °
-------------	-----------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

#### Use conditions

---

Operating temperature

-5...60 °C