



L43829010

External corner for GBD 56x175mm of PVC in pure white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	GBD
-----------------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	56 mm
Length	45 mm
Trunking width	175 mm

Cover, door

Lid mounting	External
Lid with softlip	No
Number of lids mountable	2

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	83 / 140 °
-------------	------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-5...60 °C