



L43919010

Internal corner for GBD 56x134mm of ABS in pure white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	GBD
-----------------------	-----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	56 mm
Length	110 mm
Trunking width	134 mm

Cover, door

Lid with softlip	No
Number of lids mountable	0

Materials

RAL colour	RAL 9010 - Pure white
Material	ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	83 / 97 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Halogen free

No

Use conditions

Operating temperature

-30...90 °C