



L4391ALU

Internal corner for GBD(A) 56x134mm of ABS aluminium

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 56 mm

Trunking width 134 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -30...90 °C