



L4392ALU

**External corner for GBD(A) 56x134mm of ABS aluminium**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 56 mm

Trunking width 134 mm

**Cover, door**

Lid mounting External

Lid with softlip No

Number of lids mountable 2

**Materials**

Colour aluminium

Material ABS

Material group plastic

Type of surface treatment wet painted

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 83 / 140 °

**Accessories included**

Accessory configuration Moulded

**Standards**

Approvals EN50085-2-1

European directive RoHs voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

---

Operating temperature

-30...90 °C