



L4398ALU

**Flat angle, GBD(A)50131, alu colour**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	65 mm
-----------------	-------

Trunking width	130 mm
----------------	--------

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

Colour	aluminium
--------	-----------

Material	ABS
----------	-----

Material group	plastic
----------------	---------

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

**Use conditions**

Operating temperature	-30...90 °C
-----------------------	-------------