



L44119010

**Internal corner for GBD 56x207mm of ABS in pure white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility GBD

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 56 mm

Length 110 mm

Trunking width 207 mm

**Cover, door**

Lid with softlip No

Number of lids mountable 0

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 83 / 97 °

**Accessories included**

Accessory configuration Moulded

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

**Use conditions**

Operating temperature -30...90 °C