



L44149010

Internal corner for GBD 56x207mm of ABS in pure white

Technical properties

Architecture

Fixing mode Glued

Configuration

Antibacterial treatment No

Compatibility

Product compatibility GBD

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 56 mm

Trunking width 207 mm

Cover, door

Lid with softlip No

Number of lids mountable 0

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 97 / 140 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Use conditions

Operating temperature -30...90 °C