



L4472ALU

**External corner for GBD(A) 56x85mm of ABS aluminium**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	56 mm
-----------------	-------

Trunking width	85 mm
----------------	-------

**Cover, door**

Lid mounting	External
--------------	----------

Lid with softlip	No
------------------	----

Number of lids mountable	1
--------------------------	---

**Materials**

Colour	aluminium
--------	-----------

Material	ABS
----------	-----

Material group	plastic
----------------	---------

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	83 / 140 °
-------------	------------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

**Use conditions**

Operating temperature	-30...90 °C
-----------------------	-------------