



L4472ALU

**External corner for GBD(A) 56x85mm of ABS aluminium**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 56 mm

Trunking width 85 mm

**Cover, door**

Lid mounting External

Lid with softlip No

Number of lids mountable 1

**Materials**

Colour aluminium

Material group plastic

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 83 / 140 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Use conditions**

Operating temperature -30...90 °C