



L4478ALU

Flat angle for GBD(A) 56x85mm of ABS aluminium

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	56 mm
-----------------	-------

Trunking width	85 mm
----------------	-------

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	aluminium
--------	-----------

Material	ABS
----------	-----

Material group	plastic
----------------	---------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-30...90 °C
-----------------------	-------------