



L6812VERZ



External corner, FWK 30/50060,galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	150 mm
Internal width	59 mm
Trunking width	100 mm
Measure a	150 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	steel, plaster
Type of surface treatment	Galvanised

Mecanic features

Bending angle	105 °
---------------	-------

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	2950 mm ²
-------------------------------	----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90