



L6815VERZ



Flat corner, FWK 30/50060, galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	250 mm
Internal width	59 mm
Trunking width	100 mm
Measure a	250 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	zinc coated
Material group	steel, plaster
Type of surface treatment	Galvanised

Mecanic features

Bending angle	90 °
---------------	------

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	2950 mm²
-------------------------------	----------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

REACH conform	Yes
RoHS conform	Yes
certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90