



L6821VERZ



Internal corner, FWK 30/50110,galvanized

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Internal height 50 mm

Trunking height 88 mm

Length 240 mm

Internal width 109 mm

Trunking width 150 mm

Measure a 240 mm

Cover, door

Lid with softlip -

Materials

Material group steel, plaster

Type of surface treatment Galvanised

Mecanic features

Bending angle 90 °

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 5450 mm²

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Safety

certificationnormfireprotductsystem DIN 4102-11

classificationnormfireprotductsystem DIN 4102-11

Fire resistance class I 90