


L6826VERZ



T piece, FWK 30/50110, galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	300 mm
Internal width	109 mm
Trunking width	150 mm
Measure a	300 mm
Measure b	500 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	steel, plaster
Type of surface treatment	Galvanised

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	5450 mm ²
-------------------------------	----------------------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90