



L6851VERZ



**Internal corner, FWK 30/50210,galvanized**

**Technical properties**

**Architecture**

Fixing mode	Screwed
-------------	---------

**Dimensions**

Internal height	50 mm
Trunking height	88 mm
Length	240 mm
Internal width	209 mm
Trunking width	250 mm
Measure a	240 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Colour	zinc coated
Type of surface treatment	Galvanised

**Mecanic features**

Bending angle	90 °
---------------	------

**Installation, mounting**

Base punching	With base punching
---------------	--------------------

**Cable**

Internal/useful cross section	10450 mm <sup>2</sup>
-------------------------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Safety**

REACH conform	Yes
RoHS conform	Yes
certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90