



L6856VERZ



**T piece, FWK 30/50210, galvanized**

**Technical properties**

**Dimensions**

Internal height	50 mm
Trunking height	88 mm
Length	400 mm
Internal width	209 mm
Trunking width	250 mm
Measure a	400 mm
Measure b	500 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Material group	steel, plaster
----------------	----------------

**Installation, mounting**

Base punching	With base punching
---------------	--------------------

**Cable**

Internal/useful cross section	10450 mm <sup>2</sup>
-------------------------------	-----------------------

**Accessories included**

Accessory configuration	Base and lid
-------------------------	--------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
certificationnormfireproductsystem	DIN 4102-11
classificationnormfireproductsystem	DIN 4102-11
Fire resistance class	I 90