



L6862VERZ



**External corner,FWK 30/99160, galvanized**

**Technical properties**

**Architecture**

Fixing mode	Screwed
-------------	---------

**Dimensions**

Internal height	102 mm
Trunking height	142 mm
Length	150 mm
Internal width	159 mm
Trunking width	200 mm
Measure a	150 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Material group	steel, plaster
Type of surface treatment	Galvanised

**Mecanic features**

Bending angle	108 °
---------------	-------

**Installation, mounting**

Base punching	With base punching
---------------	--------------------

**Cable**

Internal/useful cross section	16218 mm <sup>2</sup>
-------------------------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Base and lid
-------------------------	--------------

**Safety**

certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90