



L6865VERZ



Flat corner, FWK 30/99160, galvanized

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Internal height 102 mm

Trunking height 142 mm

Length 350 mm

Internal width 159 mm

Trunking width 200 mm

Measure a 350 mm

Cover, door

Lid with softlip -

Materials

Material group steel, plaster

Type of surface treatment Galvanised

Mecanic features

Bending angle 90 °

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 16218 mm²

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Safety

certificationnormfireprotductsystem DIN 4102-11

classificationnormfireprotductsystem DIN 4102-11

Fire resistance class I 90