



L6871VERZ



Internal corner,FWK 30/99260, galvanized

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Internal height 102 mm

Trunking height 142 mm

Length 293 mm

Internal width 259 mm

Trunking width 300 mm

Measure a 293 mm

Cover, door

Lid with softlip -

Materials

Material group steel, plaster

Type of surface treatment Galvanised

Mecanic features

Bending angle 90 °

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 26418 mm²

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Safety

certificationnormfireprotductsystem DIN 4102-11

classificationnormfireprotductsystem DIN 4102-11

Fire resistance class I 90