



L6876VERZ



T piece, FWK 30/99260, galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	102 mm
Trunking height	142 mm
Length	450 mm
Internal width	259 mm
Trunking width	300 mm
Measure a	450 mm
Measure b	500 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	steel, plaster
Type of surface treatment	Galvanised

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	26418 mm ²
-------------------------------	-----------------------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90