



L6912VERZ



External corner,FWK 90/50060, galvanized

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Internal height 49 mm

Trunking height 142 mm

Length 150 mm

Internal width 54 mm

Trunking width 150 mm

Measure a 150 mm

Cover, door

Lid with softlip -

Materials

Material group steel, plaster

Type of surface treatment Galvanised

Mecanic features

Bending angle 100 °

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 2646 mm²

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Safety

certificationnormfireprotductsystem DIN 4102-12

classificationnormfireprotductsystem DIN 4102-12

Fire resistance class E 30 - E 60