



L6915VERZ



**Flat corner, FWK 90/50060, galvanized**

**Technical properties**

**Architecture**

Fixing mode	Screwed
-------------	---------

**Dimensions**

Internal height	49 mm
Trunking height	142 mm
Length	300 mm
Internal width	54 mm
Trunking width	150 mm
Measure a	300 mm

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Material group	steel, plaster
Type of surface treatment	Galvanised

**Mecanic features**

Bending angle	90 °
---------------	------

**Installation, mounting**

Base punching	With base punching
---------------	--------------------

**Cable**

Internal/useful cross section	2646 mm <sup>2</sup>
-------------------------------	----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Base and lid
-------------------------	--------------

**Safety**

certificationnormfireprotductsystem	DIN 4102-12
classificationnormfireprotductsystem	DIN 4102-12
Fire resistance class	E 30 - E 60