



L6922VERZ



External corner,FWK 90/50110, galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	49 mm
Trunking height	142 mm
Length	150 mm
Internal width	104 mm
Trunking width	200 mm
Measure a	150 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Material group	steel, plaster
Type of surface treatment	Galvanised

Mecanic features

Bending angle	104 °
---------------	-------

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	5096 mm ²
-------------------------------	----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

certificationnormfireprotductsystem	DIN 4102-12
classificationnormfireprotductsystem	DIN 4102-12
Fire resistance class	E 30 - E 60