



L6925VERZ



**Flat corner, FWK 90/50110, galvanized**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Dimensions**

Internal height 49 mm

Trunking height 142 mm

Length 350 mm

Internal width 104 mm

Trunking width 200 mm

Measure a 350 mm

**Cover, door**

Lid with softlip -

**Materials**

Material group steel, plaster

Type of surface treatment Galvanised

**Mecanic features**

Bending angle 90 °

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 5096 mm<sup>2</sup>

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Base and lid

**Safety**

certificationnormfireprotductsystem DIN 4102-12

classificationnormfireprotductsystem DIN 4102-12

Fire resistance class E 30 - E 60