




L6956VERZ



T piece, FWK 90/50210, galvanized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Internal height	49 mm
Trunking height	142 mm
Length	450 mm
Internal width	204 mm
Trunking width	300 mm
Measure a	450 mm
Measure b	500 mm

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	zinc coated
Material	Steel / Plaster
Material group	steel, plaster
Type of surface treatment	Galvanised

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	9996 mm ²
-------------------------------	----------------------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Safety

REACH conform	Yes
RoHS conform	Yes
certificationnormfireprotductsystem	DIN 4102-12
classificationnormfireprotductsystem	DIN 4102-12
Fire resistance class	E 30 - E 60