



L8081ELN

Internal corner for BRAP 80x200mm of aluminium natural anodized

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	BRAP
-----------------------	------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	80 mm
Length	150 mm
Trunking width	200 mm

Cover, door

Lid with softlip	No
Number of lids mountable	2

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base
-------------------------	------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Use conditions

Operating temperature	-30...90 °C
-----------------------	-------------