




L87629010



External corner, FB 80130, pure white

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Product compatibility	FB
-----------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	82 mm
Trunking width	130 mm
Measure a	160 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Base and lid
-------------------------	--------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
REACH conform	No
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C