



L87657030



**Flat corner, FB 80130, grey**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility FB

**Dimensions**

Trunking height 82 mm

Trunking width 130 mm

Measure a 176 mm

**Cover, door**

Lid with softlip No

**Materials**

Colour stone grey

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 90 °

**Accessories included**

Accessory configuration Base and lid

**Safety**

Protection index IP IP20

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C