



L96857030



L 9685 Grey 7030 Flat corner

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Compatibility

Product compatibility FB

Dimensions

Trunking height 100 mm

Trunking width 230 mm

Measure a 300 mm

Cover, door

Lid with softlip No

Materials

Colour stone grey

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Base and lid

Safety

Protection index IP IP20

Impact strength IK07

Use conditions

Operating temperature -5...60 °C