



LF1001008014



Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	10 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	12 mm
----------------	-------

Distance bottom-punch along trunking-direction	125 mm
--	--------

Cover, door

Lid shape	premounted
-----------	------------

Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Transparent	No
-------------	----

Cable

Internal/useful cross section	84 mm ²
-------------------------------	--------------------

Equipment

Compartment quantity	1
----------------------	---

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK06
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------